




• Da utilizzare in accoppiamento con le prolunghe tubolari 92BA

		art.	 mm	$\varnothing$ mm	H mm	L mm	L1 mm	S mm	
	<b>000910824</b>	91BA 24	24	38	29,0	180	555	17	475
	<b>000910827</b>	91BA 27	27	42	31,0	190	560	17	530
	<b>000910830</b>	91BA 30	30	48	33,0	200	565	18	580
	<b>000910832</b>	91BA 32	32	49	34,0	235	729	18	795
	<b>000910836</b>	91BA 36	36	54	35,0	245	735	20	900
	<b>000910841</b>	91BA 41	41	62	40,0	265	748	21	1060
★	<b>000910846</b>	91BA 46	46	69	42,5	280	911	23	1480
★	<b>000910850</b>	91BA 50	50	75	43,0	290	921	25	1690
★	<b>000910855</b>	91BA 55	55	82	46,0	300	924	28	1850

